



## Description & features

- VariColour filter blocked warning system
- Highest grade HEPA and carbon technology
- Automatic electronic flow control - maintains a constant extraction rate even as the filter blocks
- Quiet in operation
- Simple to install and easy to relocate

## Filters



Main Filter Code

110553

Description

HEPA



Main Filter Code

110548

Description

Carbon



Main Filter Code

111118

Description

F8/F9 Labyrinth



Pre-Filter Code

111114

Description

Cascade

## Specifications

Voltage		90v - 235v
Part Number	OEL4110	
Wattage	1.1kW	
Frequency	50Hz / 60Hz	
Cabinet Height	715mm	
Cabinet Width	975mm	
Cabinet Depth	700mm	
Cabinet Weight	70kg	
Airflow	350m <sup>3</sup> /h	
Sound Level	<60dBa	

## Machine supplied with

• 2 x Main Filter • 2 x Pre-filter • 1 x Connection Kit • 1 x Power Cable • 1 x Manual

Find out more: [Wpurex.co.uk](http://Wpurex.co.uk) | [T +44 \(0\)1405 746030](tel:+44(0)1405746030) | [E purex@purex.co.uk](mailto:epurex@purex.co.uk)

Registered Office: Purex International Limited, QWP House, Island Drive, Capitol Park, Thorne, Doncaster DN8 5UE  
 Registered No. 5136616 England | VAT No. GB842 5025 49 | WEEE Producer Registration Number: WEE/CE0067TX  
 \*Goods are subject to change | \*Illustrations are 3D created visual representations

## Connection kits

If you do not see a connection kit that fits your machine or pipework, please contact Purex or your representative

**100107**

Hose End Diameter	Hose Length	Purex Inlet Diameter
100mm	3m	100mm

Connect to 100mm diameter pipe/port

3.0m

**100105**

Hose End Diameter	Hose Length	Purex Inlet Diameter
100mm	2m	100mm

Connect to 100mm diameter pipe/port

2.0m

**120270**

Hose End Diameter	Hose Length	Purex Inlet Diameter
100mm	1.5m	100mm

Connect to 100mm diameter pipe/port

1.5m

**120292**

Hose End Diameter	Hose Length	Purex Inlet Diameter
80mm	1.3m	100mm

Connect to 80mm diameter pipe/port

1.0m

LASER

0.3m

Ebase

**100194**

Hose End Diameter	Hose Length	Purex Inlet Diameter
50mm	2.5m	100mm

Connect to 50mm diameter pipe/port or Purex valve

2m

0.5m

**100193**

Hose End Diameter	Hose Length	Purex Inlet Diameter
50mm	3m	100mm

Connect to 50mm diameter pipe/port or Purex valve

3m

## Interfacing

Interfacing can remotely start the Purex machine when the connected machine starts.

Interfacing can also warn the connected machine when the Purex machine is in alarm.

Your Machine

10011010



Extractor

10011010

Take a look through our Interfacing Guide to see our extensive range of options