


# IFUME 400i

Moderate, **hand & machine soldering** extraction

**PUREX**  
CLEAN AIR FOR EVERYONE



## Description & features

- Full colour touch screen display
- Highest grade HEPA and carbon technology
- Automatic electronic flow control - maintains a constant extraction rate even as the filter blocks
- Gas and particle sensors to warn the operator
- Operate worldwide with no loss of performance

## Filters



Main Filter Code

113505C

Description

HEPA/Chemical



Pre-Filter Code

111057

Description

F6 Labyrinth

## Specification

Voltage	100v - 230v
Vacuum Part Number	1704002
Wattage	1.1kW
Frequency	50Hz / 60Hz
Cabinet Height	1070mm
Cabinet Width	465mm
Cabinet Depth	528mm
Cabinet Weight	60kg
Airflow	400m3/h
Sound Level	<60dBa

## Machine supplied with

• 1 x Main Filter • 1 x Pre-filter • 1 x Connection Kit • 1 x Power Cable • 1 x Manual

Find out more: **W** [purex.co.uk](http://purex.co.uk) | **T** +44 (0)1405 746030 | **E** [purex@purex.co.uk](mailto:purex@purex.co.uk)

Registered Office: Purex International Limited, QWP House, Island Drive, Capitol Park, Thorne, Doncaster DN8 5UE  
Registered No. 5136616 England | VAT No. GB842 5025 49 | WEEE Producer Registration Number: WEE/CE0067TX  
\*Goods are subject to change | \*Illustrations are 3D created visual representations

# IFUME 400i

Moderate, **hand & machine soldering** extraction

## Options







### Main filter

Code	Description		
113508	Chemical	113668	HEPA / Twin Chemical
113505P	Chemical	113512	HEPA / Chemical (Cleanroom)
113579	Chemical Special	113669	HEPA / Chemical (Cleanroom)
113662	CSA Chemical	113505H	HEPA (Hydrophobic)
113809	HEPA	113513	Solvent Lock
	113531	Pleated Bag	

### Pre-filter

200524	F8 / F9 Pad
--------	-------------


### Connection kits

100032			100043			100171		
Hose End Diameter	Hose Length	Purex Inlet Diameter	Hose End Diameter	Hose Length	Purex Inlet Diameter	Hose End Diameter	Hose Length	Purex Inlet Diameter
50mm	3m	80mm	50mm	6m	80mm	125mm	3m	80mm
Connect to 50mm diameter pipe/port or Purex valve 			Connect to 50mm diameter pipe/port or Purex valve 			Connect to 125mm diameter pipe/port 		
	3.0m			6.0m			2.5m	
120288			120297			120299		
Hose End Diameter	Hose Length	Purex Inlet Diameter	Hose End Diameter	Hose Length	Purex Inlet Diameter	Hose End Diameter	Hose Length	Purex Inlet Diameter
100mm	2.3m	80mm	100mm	2m	80mm	80mm	3m	80mm
Connect to 100mm diameter pipe/port 			Connect to 100mm diameter pipe/port or Purex valve 			Connect to 80mm diameter pipe/port 		
	0.3m			2.0m			3.0m	

### Interfacing

Interfacing can remotely start the Purex machine when the connected machine starts.

Interfacing can also warn the connected machine when the Purex machine is in alarm.



Take a look through our [Interfacing Guide](#) to see our extensive range of options