

2000i

Large, multi-use fume extraction unit

PUREX
CLEAN AIR FOR EVERYONE



Description & features

- Clear & informative graphic display
- Highest grade HEPA and carbon technology
- Automatic electronic flow control - maintains a constant extraction rate even as the filter blocks
- Gas and particle sensors to warn the operator
- Adjustable airflow

Filters



Main Filter Code

110615

Description

HEPA/Chemical



Pre-Filter Code

111037

Description

F6 Labyrinth

Specification

| Voltage | 3 phase supply | |
|--------------------|-----------------------|----------|
| | 220v | 400v |
| Volume Part Number | 0LX2011D | 0LX2010D |
| Vacuum Part Number | 0221211D | 0221201D |
| Wattage | 3kW | |
| Frequency | 50Hz / 60Hz | |
| Cabinet Height | 1400mm | |
| Cabinet Width | 725mm | |
| Cabinet Depth | 726mm | |
| Cabinet Weight | 150kg | |
| Airflow | 2000m ³ /h | |
| Sound Level | <60dBa | |

Machine supplied with

• 1 x Main Filter • 1 x Pre-filter • 1 x Power Cable • 1 x Manual • 1 x 4.5m fixed power cable (no plug)

Find out more: Wpurex.co.uk | [T +44 \(0\)1405 746030](tel:+44(0)1405746030) | [E purex@purex.co.uk](mailto:purex@purex.co.uk)

Registered Office: Purex International Limited, QWP House, Island Drive, Capitol Park, Thorne, Doncaster DN8 5UE
Registered No. 5136616 England | VAT No. GB842 5025 49 | WEEE Producer Registration Number: WEE/CE0067TX
*Goods are subject to change | *Illustrations are 3D created visual representations

2000i

Large, multi-use fume extraction unit

Options

Main filter

Pre-filter

Connection kits

| Code | Description | Code | Description |
|--------|-----------------------------|--------|----------------------|
| 110614 | Chemical | 110610 | HEPA / Twin Chemical |
| 110632 | HEPA / Chemical (Cleanroom) | 110619 | HEPA |
| 111099 | F8 / F9 Labyrinth | | |

If you do not see a connection kit that fits your machine or pipework, please contact Purex or your representative

120280

| Hose End Diameter | Hose Length | Purex Inlet Diameter |
|-------------------|-------------|----------------------|
| 150mm | 1.5m | 150mm |

Connect to 150mm diameter pipe/port

120287

| Hose End Diameter | Hose Length | Purex Inlet Diameter |
|-------------------|-------------|----------------------|
| 100mm | 3m | 150mm |

Connect to 100mm diameter pipe/port

Large Extraction Arm (Oskar Arm)

| Hose End Diameter | Hose Length | Purex Inlet Diameter |
|-------------------|-------------|----------------------|
| 315mm | 3m | 150mm |

LARGE EXTRACTION ARM


Our 2m long extraction arm with it's triple axis can be used in a variety of applications. The flexibility of the arm allows it to be manoeuvred to reduce restriction and has a large hood of 315mm at the inlet.

CODE: 840197 - Extraction arm
CODE: 840198 - Mounting bracket
CODE: 840199 - 150mm Connection flange
CODE: 120280 - 150mm Hose kit

Interfacing

Interfacing can remotely start the Purex machine when the connected machine starts.

Interfacing can also warn the connected machine when the Purex machine is in alarm.



Take a look through our Interfacing Guide to see our extensive range of options